

TECHSPEC®

0.15X MercuryTL™ Liquid Lens Telecentric Lens



0.15X MercuryTL™ Liquid Lens Telecentric Lens, #36-188



Stock **#36-188** 3-4 DAYS



1



£1,810.50

ADD TO CART

Qty 1+

£1,810.50

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Length excluding Threads (mm):  
186.70

Horizontal Field of View, 1/2" Sensor:  
41.2mm

Filter Thread:  
M62 x0.75 (Female)

Weight (g):

|                                                                                |
|--------------------------------------------------------------------------------|
| 405                                                                            |
| <b>Horizontal Field of View, 1/3" Sensor:</b><br>30.9mm                        |
| <b>Stock No. of Mounting Clamp:</b><br><a href="#">#56-871</a> Sold Separately |
| <b>Note:</b><br>MercuryTL™                                                     |
| <b>Typical Telecentricity @ 588nm (°):</b><br><0.050                           |
| <b>Typical Distortion @ 588nm (%):</b><br><0.9                                 |
| <b>Mounting Diameter (mm):</b><br>65                                           |
| <b>Type:</b><br>Telecentric Lens                                               |
| <b>Primary Magnification PMAG:</b><br>0.15X                                    |
| <b>Maximum Sensor Format:</b><br>1/2"                                          |
| <b>Working Distance (mm):</b><br>169 - 265                                     |
| <b>Mount:</b><br>C-Mount                                                       |
| <b>Aperture (f/#):</b><br>f/10                                                 |
| <b>FOV @ Max Sensor Format, H x V (mm):</b><br>41.2 x 30.9                     |
| <b>Lens Wavelength Range:</b><br>VIS                                           |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |