

100X ZEISS A-Plan Objective

See More by [ZEISS](#)



ZEISS A-Plan Objectives



Stock #13-820 3-4 DAYS



1



£487.05

ADD TO CART

Qty 1+

£487.05

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Compatible Cover Glass Thickness (mm):
0.17

Field of View (mm):
0.23

Focal Length FL (mm):
1.60

Model Number: 421090-9800-000
Length excluding Threads (mm): 43.90
Magnification: 100X
Maximum Diameter (mm): 30
Numerical Aperture NA: 0.8
Mounting Threads: M27 x0.75
Compatible Tube Lens Focal Length (mm): Focal Length: 164.50mm
Type: Microscope Objective
Typical Applications: Fluorescence, BrightField
Resolving Power (µm): 0.34
Depth of Field (µm): 0.43
Operating Temperature (°C): +10 to +40
Operating Humidity: 75% at 35°C
Working Distance (mm): 0.97
Weight (g): 164
Wavelength Range (nm): 480 - 650
Style: Infinity Corrected
Manufacturer: ZEISS
Field Number (mm): 23
Parfocal Length (mm): 45.06
Immersion Liquid: N/A

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View