

100mm Diameter 600 Grit Ground Glass Diffuser



Stock **#38-790**

3-4 DAYS

-

1

+

£49.30

ADD TO CART

Qty 1-10
£49.30
Qty 11+
£44.41
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):

100.00 ±0.25

Coating:

Uncoated

Edges:

Seamed Edges

Grit:

600

Substrate: ☐
Float Glass

Thickness (mm):
1.60

Type:
Ground Glass Diffuser

Wavelength Range (nm):
350 - 2000

Note:
Sandblasted on first surface

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 233:
[Compliant](#)
