

10.1mm FL, No IR-Cut Filter, f/2.8, Micro Video Lens



Stock **#63-762** ☒ In Stock

-

1

+

£50.15

ADD TO CART

Qty 1-49
£50.15
Qty 50+
£39.95
Volume Pricing
Request Quote

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Length (mm):
13.40

Filter Thread:
M12 x0.50

Maximum Diameter (mm):
15.0

Maximum Image Circle (mm):

8.00
Horizontal Field of View @ Max Sensor Format: 36
Resolution, On-Axis: 81 lp/mm @ 20% Contrast
Resolution, 0.7 Field: 54 lp/mm @ 20% Contrast
Resolution, Full Field: 64 lp/mm @ 20% Contrast
Note: Standard
Type: M12 Imaging Lens
Focal Length FL (mm): 10.10
Maximum Sensor Format: 1/2"
Working Distance (mm): 400 - ∞
Mount: M12 x 0.5 (S-Mount)
Aperture (f/#): f/2.8
Distortion (%): -0.57 @ Full Field
IR Cut Filter: No
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View