

10mW, 1064nm DPSS Pointing Laser



DPSS Pointing Lasers

Stock **#37-043** ☒ In Stock

-

1

+

£303.88

ADD TO CART

Qty 1-9
£303.88

Qty 10+
£273.70

Volume Pricing
Request Quote

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Operating Temperature (°C):
23 to 27

Operating Voltage (V):
5.0

Output Power (mW):
10

Spatial Mode: TEM ₀₀
Wavelength (nm): 1,064.00 ±1
Wavelength Tolerance (nm): ±1
Power Supply: Power Supply Required and Sold Separately. USA: #83-855 Europe: #83-855 Japan: #13-640 Korea: #33-770 China: #83-855
Modulation Frequency (kHz): 0 - 10
Note: Compatible TEC Controller (#19-476) sold separately
Beam Diameter (mm): 1.0 Typical
Beam Divergence (mrad): <1 Typical
Laser Class - CDRH: IIIb
Color: Infrared
Length (mm): 90.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant