

10mm Diameter 600 Grit Ground Glass Diffuser



Stock **#38-782** 3-4 DAYS

- 1 + **£15.09**

ADD TO CART

Qty 1-10
£15.09

Qty 11+
£12.96

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
10.00 ±0.25

Coating:
Uncoated

Edges:
Ground Edges

Grit: ☐

600

Substrate: ☐
Float Glass

Thickness (mm):
1.60

Type:
Ground Glass Diffuser

Wavelength Range (nm):
350 - 2000

Note:
Sandblasted on first surface

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 233:
[Compliant](#)
