

35mm Focal Length Lens, 1.1" Sensor Format



Compact Fixed Focal Length Lenses for 1.1" Sensors

Stock #14-114 3-4 DAYS

[Similar Products](#)



1



£884.00

ADD TO CART

Qty 1+

£884.00

Volume Pricing

[Request Quote](#)

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Iris Option:
Variable

Length (mm):
45.20

Filter Thread:
M34 x0.50

Maximum Diameter (mm):
39.5

Weight (g): 103.0
Maximum Image Circle (mm): 17.60
Horizontal Field of View @ Max Sensor Format: 22.9°
Horizontal Field of View, 1.1" Sensor: 22.9°
Type: Fixed Focal Length Lens
Focal Length FL (mm): 35.00
Maximum Sensor Format: 1.1"
Working Distance (mm): 300 - ∞
Mount: C-Mount
Aperture (f/#): f/2.8 - f/16
Distortion (%): -0.1
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View