

8mm Focal Length Lens, 1.1" Sensor Format



Compact Fixed Focal Length Lenses for 1.1" Sensors

Stock #14-110 3-4 DAYS

[Similar Products](#)



1



£1,003.00

ADD TO CART

Qty 1+

£1,003.00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Iris Option:
Variable

Length (mm):
53.20

Maximum Diameter (mm):
57.5

Weight (g):
157.4

Maximum Image Circle (mm): 17.60
Horizontal Field of View @ Max Sensor Format: 83.0°
Horizontal Field of View, 1.1" Sensor: 83.0°
Type: Fixed Focal Length Lens
Focal Length FL (mm): 8.00
Maximum Sensor Format: 1.1"
Working Distance (mm): 200 - ∞
Mount: C-Mount
Aperture (f/#): f/2.8 - f/16
Distortion (%): -0.6
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View