

11 x 11mm, 1550nm, Corning Polarcor™ Glass Polarizer



Corning Polarcor™ Glass Polarizers

Stock #13-623 3-4 DAYS



1



£701.25

ADD TO CART

Qty 1+

£701.25

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle of Incidence (°):
0 ±5

Coating:
BBAR (1510-1590nm)

Design Wavelength DWL (nm):
1550

Extinction Ratio:
>100,000:1

Substrate: Borosilicate Glass Containing Elongated Silver Crystals
Length (mm): 11.00
Minimum Transmission (%): >98.5
Dimensions (mm): 11.0 x 11.0
Surface Quality: 40-20
Thickness (mm): 0.50 ±0.05
Dimensional Tolerance (mm): ±0.1
Coating Specification: R_{avg} <0.25% @ 1510 - 1590nm
Wavelength Range (nm): 1510 - 1590
Width (mm): 11.00
Insertion Loss (dB): <0.06
Index of Refraction n_d: 1.5051
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 6.5
Knoop Hardness (kg/mm²): 480
Young's Modulus (GPa): 58.605
Poisson's Ratio: 0.21
Abbe Number (v_d): 57.6
Density (g/cm³): 2.412

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View