

120 lp/mm 1" x 3", Opal Glass Ronchi Ruling Slide



Stock **#59-550** ☐ In Stock

-

1

+

£265.20

ADD TO CART

Qty 1-4
£265.20
Qty 5+
£252.19
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Coating:

Vacuum Deposited Chrome

Dimensional Tolerance (inches):

±0.100

Frequency (lp/mm):

120.00

Substrate:

Opal Glass
Length (mm): 25.40
Optical Density OD (Average): >3.0
Pattern Size (mm): 12.7 x 25.4
Surface Quality: 40-20
Thickness (mm): 1.52 ±0.100
Width (mm): 76.20
Note: Pattern Location is Centered
NIST Certification: No
Line Width Tolerance (µm): ±0.001

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant