

TECHSPEC® 12.5 x 17.68 x 1mm VIS, Elliptical Plate Beamsplitter



Elliptical Plate Beamsplitters

Stock **#48-913** 3-4 DAYS



1



£124.10

ADD TO CART

Qty 1-5

£124.10

Qty 6+

£112.20

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Clear Aperture (%):
>85

Coating:
VIS

Coating Specification:
Surface 1: 50R/50T (R_{abs} ±5% @ 550nm, R_{avg} ±10%)

@400 - 700nm) Surface 2: R _{avg} ≤1.0%, R _{abs} ≤2.0% @400 - 700nm
Construction: Plate
Edges: Cut with 0.25mm Maximum Edge Chip
Major Axis (mm): 18.68 +0.0/-0.40 (physical length)
Minor Axis (mm): 12.50 +0.0/-0.10
Parallelism (arcmin): <1
Reflection/Transmission Ratio (R/T): 50/50
Substrate: N-BK7
Surface Flatness (P-V): <2λ(per inch)
Surface Quality: 60-40
Thickness (mm): 1.00
Thickness Tolerance (mm): ±0.25
Type: Standard Beamsplitter
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant