

12.5mm Diameter 600 Grit Ground Glass Diffuser



Stock **#38-784** [CONTACT US](#)

-

1

+

£10.41

ADD TO CART

Qty 1-10
£10.41
Qty 11+
£9.56
Volume Pricing
Request Quote

ⓘ

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
12.50 ±0.25

Coating:
Uncoated

Edges:
Ground Edges

Grit:

600

Substrate: ☐
Float Glass

Thickness (mm):
1.60

Type:
Ground Glass Diffuser

Wavelength Range (nm):
350 - 2000

Note:
Sandblasted on first surface

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 233:
[Compliant](#)
