

TECHSPEC[®] 12.5mm Uncoated Ultra Precision UV Fused Silica Right Angle Prism



Stock #35-903 3-4 DAYS

-

1

+

£236.30

ADD TO CART

Qty 1-5

£236.30

Qty 6+

£212.67

Volume Pricing

[Request Quote](#)

!

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle Tolerance (arcsec):
±15

Coating:
Uncoated

Substrate: ☐
[Fused Silica](#) (Coming 7980)

Surface Quality: 20-10
Type: Right Angle Prism
Dimensional Tolerance (mm): +0.00/-0.10
Bevel: Protective bevel as needed
Clear Aperture (%): 90
Length of Hypotenuse (mm): 17.70
Length of Legs (mm): 12.50
Pyramid Tolerance (arcmin): ±1
Image Orientation: Left-Handed
Wavelength Range (nm): 200 - 2200
Surface Flatness (P-V): λ/20

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View