

TECHSPEC® 12.5mm H x 25mm L x 20mm FL Uncoated, Illumination Grade PCX Cylinder Lens



Stock **#68-031** 3-4 DAYS

- 1 + **£52.70**

ADD TO CART

Qty 1-5
£52.70
Qty 6+
£42.07
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Effective Focal Length EFL (mm):
20.00

Substrate:
[N-BK7](#)

f/#:
1.6

Numerical Aperture NA: 0.31
Coating: Uncoated
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 350 - 2200
Back Focal Length BFL (mm): 17.63
Center Thickness CT (mm): 3.60
Center Thickness Tolerance (mm): ±0.1
Dimensional Tolerance (mm): +0.0/-0.2
Dimensions (mm): 12.5 x 25.0
Edge Thickness ET (mm): 1.50
Focal Length Tolerance (%): ±3
Radius R₁ (mm): 10.34
Surface Quality: 60-40

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View