

TECHSPEC® 12.5mm H x 25mm L x 50mm FL Uncoated, Illumination Grade PCX Cylinder Lens



Stock **#68-033** 3-4 DAYS

- 1 + **£52.70**

ADD TO CART

Qty 1-5
£52.70

Qty 6+
£42.07

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Effective Focal Length EFL (mm): 50.00
Substrate: N-BK7
f/#: 4

Numerical Aperture NA: 0.13
Coating: Uncoated
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 350 - 2200
Back Focal Length BFL (mm): 48.68
Center Thickness CT (mm): 2.00
Center Thickness Tolerance (mm): ±0.1
Dimensional Tolerance (mm): +0.0/-0.2
Dimensions (mm): 12.5 x 25.0
Edge Thickness ET (mm): 1.23
Focal Length Tolerance (%): ±3
Radius R₁ (mm): 25.84
Surface Quality: 60-40

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View