

20° Travel, 60 x 60mm Stage Size Metric Goniometer, R130.4



Stock **#13-630** 3-4 DAYS



1



£664.70

ADD TO CART

Qty 1-4

£664.70

Qty 5+

£598.23

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Goniometer

Guide System:
Dovetail

Type of Drive:
Lead Screw

Type:

Metric
Stage Size (mm): 60 x 60
Travel (°): ±10
Construction: Brass Stage
Load Capacity (kg): 5
Mounting Threads: (1) M6 x 1.0, (8) M4 x 0.7
Radius R (mm): 130.4
Resolution (°): 0.1
Weight (kg): 0.70

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant