

20X ZEISS A-Plan Objective

See More by [ZEISS](#)



ZEISS A-Plan Objectives



Stock **#13-817** [CONTACT US](#)



1



£274.55

ADD TO CART

Qty 1+
£274.55

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Compatible Cover Glass Thickness (mm):
0.17

Field of View (mm):
1.15

Focal Length FL (mm):
8.20

Model Number: 421050-9900-000
Length excluding Threads (mm): 44.40
Magnification: 20X
Maximum Diameter (mm): 30
Numerical Aperture NA: 0.45
Mounting Threads: M27 x0.75
Compatible Tube Lens Focal Length (mm): Focal Length: 164.50mm
Type: Microscope Objective
Typical Applications: Fluorescence, BrightField, Polarization-Optical DIC
Resolving Power (µm): 0.61
Depth of Field (µm): 1.36
Operating Temperature (°C): +10 to +40
Operating Humidity: 75% at 35°C
Working Distance (mm): 0.46
Weight (g): 130
Wavelength Range (nm): 480 - 650
Style: Infinity Corrected
Manufacturer: ZEISS
Field Number (mm): 23
Parfocal Length (mm): 45.06
Immersion Liquid: N/A

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View