

TECHSPEC® 20mm, Aluminum & VIS 0° Coated, N-BK7 Right Angle Prism



N-BK7 Right Angle Prisms

Stock **#48-551** ☐ In Stock

1 **£75.65**

ADD TO CART

Qty 1-5
£75.65

Qty 6+
£68.08

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating:
VIS 0° & Aluminized

Substrate: ☐
[N-BK7](#)

Surface Quality:
60-40

Type: Right Angle Prism
Dimensional Tolerance (mm): ±0.1
Angle Tolerance (arcmin): ±2
Bevel: Protective bevel as needed
Length of Hypotenuse (mm): 28.30
Length of Legs (mm): 20.00
Image Orientation: Left-Handed
Coating Specification: Hypotenuse: R _{avg} >85% @ 400 - 700nm Legs: R _{avg} ≤0.4% @ 425 - 675nm
Ray Deviation (°): 90
Wavelength Range (nm): 425 - 675
Damage Threshold, By Design: ☐ Hypotenuse: 0.3 J/cm ² @ 532nm & 1064nm, 10ns Legs: 5 J/cm ² @ 532nm, 10ns
Power (fringes) @ 632.8nm: 1.25
Irregularity (fringes) @ 632.8nm: 0.50

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View