

Hoya R-60 (600nm), 22mm CA, C-Mount Longpass Glass Color Filter



22mm CAC-Mount Longpass Glass Color Filter

Stock #13-032 3-4 DAYS

-

1

+

£79.05

ADD TO CART

Qty 1-9

£79.05

Qty 10+

£70.55

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.40 +0/-0.25

Clear Aperture CA (mm):
22.0

Cut-Off Position λ_c (nm):
600±6

Cut-On Wavelength (nm): 600.00
Density (g/cm³): 2.69
Glass/Filter Number: Hoya R-60
Substrate: ☐ Colored Glass
Coating: Uncoated
Color: Red
Passband Limit 1 λ_{p1} (nm): 620.00
Spectral Transmittance t_p (%): 93.00
Stopband Limit λ_s(nm): 558.00
Surface Quality: 80-50
Transformation Temperature (°C): 560.00
Type: Longpass Filter
Wavelength: VIS
Reflection Factor P_d: 0.92
Substrate Thickness (mm): 2.50 ±0.2
Thread Type: C-Mount
Total Length (mm): 20.3
Mount Diameter (mm): 30.0
Filter Included: #66-054
Mount Included: #56-353

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View