

22mm CA, Schott N-WG-320, C-Mount Longpass Glass Color Filter



22mm CAC-Mount Longpass Glass Color Filter

Stock #13-026 3-4 DAYS

-

1

+

£79.05

ADD TO CART

Qty 1-9

£79.05

Qty 10+

£70.55

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):

25.40 ±0.38

Clear Aperture CA (mm):

22.0

Cut-Off Position λ_c (nm):

320±6

Cut-On Wavelength (nm): 320.00
Density (g/cm³): 2.51
Glass/Filter Number: SCHOTT N-WG320
Substrate: ☐ Colored Glass
Coating: Uncoated
Color: Clear
Passband Limit 1 λ_{p1} (nm): 470.00
Spectral Transmittance t_p (%): 92
Stopband Limit λ_s(nm): 280.00
Surface Quality: 80-50
Transformation Temperature (°C): 563.00
Type: Longpass Filter
Wavelength: UV
Reflection Factor P_d: 0.92
Substrate Thickness (mm): 3.00 ±0.2
Thread Type: C-Mount
Total Length (mm): 20.3
Mount Diameter (mm): 30.0
Filter Included: #46-420
Mount Included: #56-353

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View