

232nm, 10nm FWHM, 50mm Dia. First Surface UV Bandpass Filter



UV Bandpass Filters

Stock **#14-917** CLEARANCE 3-4 DAYS



1



£231.16

ADD TO CART

Qty 1+

£231.16

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
50.00 +0.00/-0.25

Angle of Incidence (°):
0

Optical Density OD (Average):
4.0

Clear Aperture CA (mm):
45

Center Wavelength CWL (nm):

232.00 +3.0/-0
Full Width-Half Max FWHM (nm): 10.00 ±2
Substrate: ☐ Fused Silica (Corning 7980)
Minimum Transmission (%): 15
Coating: First Surface
Surface Quality: 80-50
Thickness (mm): 1.50 ±0.25
Type: Bandpass Filter
Blocking Wavelength Range (nm): 200 - 2000

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View