

24" Length, Dovetail Optical Rail



12" Length, Dovetail Optical Rail, #54-401

Stock #11-159 3-4 DAYS



1



£210.80

ADD TO CART

Qty 1-4

£210.80

Qty 5+

£200.94

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Linear (X)

Guide System:
Dovetail

Type of Drive:
Manual

Type: Universal (Metric & English)
Travel (mm): 609.6
Travel (inches): 24
Length (inches): 24
Length (mm): 609.60
Construction: Black Anodized Aluminum
Mounting Threads: C'bore Holes and Slots only for 1/4" (or M6) S.H.C.S
Note: Rail

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant