

TECHSPEC[®] 24" Travel, English Long Travel Rack & Pinion Track



Rack & Pinion Track

Stock #59-335 3-4 DAYS



1



£333.20

ADD TO CART

Qty 1+

£333.20

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Linear (X)

Type of Drive:
Rack and Pinion

Type:
English

Travel (inches):
24

Construction:

Black Anodized Aluminum
Graduation (inches): 0.1
Load Capacity, Normal (kg): 5
Load Capacity, Vertical (kg): 2
Mounting Threads: N/A
Note: Track
S.H.C.S. C'bore: (10) 0.27" Thru
Straight Line Accuracy (mm): 0.1 - 0.25
Travel Per Knob Rotation (inches): 0.71

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View
