

25 x 25mm 600 Grit Ground Glass Diffuser



Stock **#38-787** 3-4 DAYS

⊖ 1 ⊕ **£17.43**

ADD TO CART

Qty 1-10
£17.43
Qty 11+
£15.30
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Coating: Uncoated
Dimensional Tolerance (mm): ±0.76
Dimensions (mm): 25.00 x 25.00
Edges:

Cut Edges
Grit: 600
Substrate: Float Glass
Thickness (mm): 1.60
Type: Ground Glass Diffuser
Wavelength Range (nm): 350 - 2000
Width (mm): 25.00
Note: Sandblasted on first surface
Length (mm): 25.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant