

25.4 x 25.4mm, 4-6λ Mirror



4-6λ First Surface Mirrors

Stock **#69-246** ☐ In Stock

-

1

+

£15.72

ADD TO CART

Qty 1-5

£15.72

Qty 6+

£12.32

Volume Pricing

[Request Quote](#)

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Surface Flatness (P-V):
4 - 6λ

Substrate: ☐
Float Glass

Surface Quality:
80-50

Dimensions (mm): 25.4 x 25.4 ±0.76
Coating Specification: R_{avg} >85% @400 - 700nm
Coating: Protected Aluminum (400-700nm)
Coating Type: Metal
Angle of Incidence (°): 45.00
Bevel: Protective as needed
Clear Aperture (%): >90
Thickness (mm): 3.00
Type: Flat Mirror
Wavelength Range (nm): 400 - 700
Length (mm): 25.40
Width (mm): 25.40

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant