

**TECHSPEC® 25.4 x 25.4mm Protected Gold, 4-6λ Mirror**



Stock **#83-496** 3-4 DAYS

- 1 + **£38.25**

ADD TO CART

|         |
|---------|
| Qty 1-5 |
| £38.25  |

|        |
|--------|
| Qty 6+ |
| £28.90 |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Surface Flatness (P-V):  
4 - 6λ

Substrate: ☐  
Float Glass

Surface Quality:  
60-40

Dimensions (mm):

|                                                                                                                  |
|------------------------------------------------------------------------------------------------------------------|
| 25.4 x 25.4                                                                                                      |
| <b>Dimensional Tolerance (mm):</b><br>±0.25                                                                      |
| <b>Coating Specification:</b><br>R <sub>avg</sub> >96% @ 700 - 2000nm<br>R <sub>avg</sub> >96% @ 2000 - 10,000nm |
| <b>Coating:</b><br>Protected Gold (700-10000nm)                                                                  |
| <b>Coating Type:</b><br>Metal                                                                                    |
| <b>Clear Aperture CA (mm):</b><br>24.13 x 24.13                                                                  |
| <b>Edges:</b><br>Seamed, 0.5mm Maximum Edge Chip                                                                 |
| <b>Thickness (mm):</b><br>3.00                                                                                   |
| <b>Type:</b><br>Flat Mirror                                                                                      |
| <b>Wavelength Range (nm):</b><br>700 - 10000                                                                     |
| <b>Length (mm):</b><br>25.40                                                                                     |
| <b>Width (mm):</b><br>25.40                                                                                      |
| <b>Damage Threshold, By Design:</b> <input type="checkbox"/><br>0.8 J/cm² @ 1064nm, 10ns                         |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |

---