

25.4mm 355nm, High Energy Polarizing Cube Beamsplitter



Laser Line High Energy Polarizing Cube Beamsplitters

Stock #33-317 3-4 DAYS



1



£969.00

ADD TO CART

Qty 1-10

£969.00

Qty 11+

£741.20

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Beam Deviation (arcmin):
<3

Clear Aperture (%):
90

Construction:
Cube

Design Wavelength DWL (nm): 355
Dimensions (mm): 25.4 x 25.4 x 25.4 +0.0/-0.3
Extinction Ratio: 1000:1
Substrate: ☐ Fused Silica (Corning 7980)
Surface Flatness (P-V): λ/6
Surface Quality: 40-20
Transmission (%): T _p >96% @ 355nm
Type: Linear Polarizer
Wavelength Range (nm): 345 - 365
Damage Threshold, By Design: ☐ Typical: 20 J/cm ² @ 1064nm 10ns, 20Hz

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant