

25.4mm 532nm, High Energy Polarizing Cube Beamsplitter



Laser Line High Energy Polarizing Cube Beamsplitters

Stock **#33-318** [CONTACT US](#)

-

1

+

£947.75

ADD TO CART

Qty 1-10
£947.75

Qty 11+
£724.20

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Beam Deviation (arcmin):
<3

Clear Aperture (%):
90

Construction:
Cube

Design Wavelength DWL (nm): 532
Dimensions (mm): 25.4 x 25.4 x 25.4 +0.0/-0.3
Extinction Ratio: 1000:1
Substrate: Fused Silica (Coming 7980)
Surface Flatness (P-V): λ/6
Surface Quality: 40-20
Transmission (%): T_p >97% @ 532nm
Type: Linear Polarizer
Wavelength Range (nm): 510 - 550
Damage Threshold, By Design: Typical: 20 J/cm² @ 1064nm 10ns, 20Hz

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant