

TECHSPEC® 25mm Dia., Enhanced Aluminum, $\lambda/10$ Stemmed Mirror



TECHSPEC® Stemmed Mirror



Stock #14-579 CLEARANCE 3-4 DAYS

-

1

+

£112.20

ADD TO CART

Qty 1-5

£112.20

Qty 6+

£89.25

Volume Pricing

[Request Quote](#)

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 +0.00/-0.10

Surface Flatness (P-V):

N10
Substrate: Fused Silica (Coming 7980)
Back Surface: Commercial Polish
Surface Quality: 20-10
Coating Specification: R _{avg} >95% @450 - 650nm
Coating: Enhanced Aluminum (450-650nm)
Coating Type: Metal
Clear Aperture (%): 90.00
Edges: Ground, protective bevel as needed
Thickness (mm): 13.00 ±0.20
Type: Stemmed Mirror
Wavelength Range (nm): 450 - 650
Compatible Kinematic Mount: #58-853
Stem Diameter (mm): 12.50 +0.00/-0.10
Stem Length (mm): 6.50 ±0.20

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View