

TECHSPEC® 25mm Dia. x 250mm FL, Uncoated, Ge Plano-Convex Lens



Stock **#69-645** 3-4 DAYS

[Other Coating Options](#)

- 1 + **£276.25**

ADD TO CART

Qty 1-5
£276.25

Qty 6+
£221.00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.1

Effective Focal Length EFL (mm):
250.00 @ 10.6µm

Back Focal Length BFL (mm):

249.25
Coating: Uncoated
Substrate: ☐ Germanium (Ge)
Surface Quality: 60-40
Centering (arcmin): <3
Center Thickness CT (mm): 3.00 ±0.10
Edge Thickness ET (mm): 2.90
Radius R₁ (mm): 750.97
Clear Aperture CA (mm): 24
f#: 10.00
Numerical Aperture NA: 0.05
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 2000 - 14000

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View