

TECHSPEC® 25mm Dia x -25mm FL, Protected Aluminum, Convex Mirror



Convex Mirrors

Stock **#87-656** 3-4 DAYS

⊖ 1 ⊕ **£40.38**

ADD TO CART

Qty 1-5
£40.38

Qty 6+
£32.30

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00

Focal Length FL (mm):
-25.00

Center Thickness CT (mm):
3.00

Clear Aperture (%) : 90.00
Coating: Protected Aluminum (400-700nm)
Coating Specification: R _{avg} >85% @ 400 - 700nm
Coating Type: Metal
Dimensional Tolerance (mm): +0.0/-0.1
Edge Thickness ET (mm): 1.41
Focal Length Tolerance (%) : ±2
Radius R (mm): 50.0
Substrate: ☐ N-BK7
Surface Accuracy: λ/2
Surface Quality: 60-40
Thickness Tolerance (mm): ±0.1
Type: Spherical Mirror
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant