

TECHSPEC®

30mm ID Standard Cage Plate with M6 for Post Mounting



30mm ID Standard Cage Plate with M6 for Post Mounting, #85-630

Stock **#85-630** ☐ In Stock

-

1

+

£34.00

ADD TO CART

Qty 1+

£34.00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Function:
Fixed

Plate Inner Diameter (mm):
30.0

Dimensions (mm):
50 Dia.

Bolt Circle Diameter for 6mm Dia. Thru (mm):
38.0

Bolt Circle Diameter for M3 C'bore (mm):

38.0
Compatible Post: M6 x 1.0
Thickness (mm): 10.0
Construction: Black Anodized Aluminum
Diameter Tolerance (mm): +0.025/-0.000 (inner diameter)

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant

