

TECHSPEC® 30mm, Side Drive, Standard Top, 0.25" Travel, English Micrometer



Stock #83-504 3-4 DAYS

- 1 + **£307.70**

ADD TO CART

Qty 1-2

£307.70

Qty 3+

£268.34

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Linear (X)

Guide System:
Crossed Roller Bearing

Type of Drive:

English Micrometer
Drive Orientation: Side Drive
Type: English
Stage Size (mm): 30 x 30
Travel (inches): 0.25
Center Hole: 1/4-20
Construction: Aluminium Stage
Leadscrew Pitch (mm): 0.635
Load Capacity (kg): 3
Mounting Threads: (1) 1/4-20, (6) 2-56
Stage Size (inches): 1.18 x 1.18
Straight Line Accuracy (µm): 2
Pitch (arcsec): 30
Yaw (arcsec): 25

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 233: Contains SVHC(s)