

TECHSPEC[®] 30mm, Center Drive, Thru-Hole, 0.25" Travel, Metric Micrometer



TECHSPEC[®] Crossed-Roller Bearing Linear Translation Stages (Thru-Hole Model)



Stock #83-509 3-4 DAYS

-

1

+

£333.20

ADD TO CART

Qty 1-2

£333.20

Qty 3+

£290.95

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Linear (X)

Guide System:
Crossed Roller Bearing

Type of Drive: Metric Micrometer
Drive Orientation: Center Drive
Type: Metric
Stage Size (mm): 30 x30
Travel (mm): 6.5
Center Hole: 5/16"-24
Construction: Aluminium Stage
Leadscrew Pitch (mm): 0.5
Load Capacity (kg): 3
Mounting Threads: (1) 5/16"-24, (6) M2 x0.4
Stage Size (inches): 1.18 x 1.18
Straight Line Accuracy (µm): 2
Pitch (arcsec): 30
Yaw (arcsec): 25

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 233: Contains SVHC(s)