


TECHSPEC® 30mm, Side Drive, Standard Top, 0.25" Travel, English Micrometer



Stock #83-504 3-4 DAYS

⊖ 1 ⊕ **£307.70**

ADD TO CART

Qty 1-2

£307.70

Qty 3+

£268.34

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Linear (X)

Guide System:
Crossed Roller Bearing

Type of Drive:
English Micrometer

Drive Orientation:
Side Drive

Type:
English

Stage Size (mm):
30 x 30

Travel (inches):
0.25

Center Hole:
1/4-20

Construction:
Aluminium Stage

Leadscrew Pitch (mm):
0.635

Load Capacity (kg):
3

Mounting Threads:
(1) 1/4-20, (6) 2-56

Stage Size (inches):
1.18 x 1.18

Straight Line Accuracy (µm):
2

Pitch (arcsec):
30

Yaw (arcsec):
25

Regulatory Compliance

RoHS 2015:
[Exempt](#)

Certificate of Conformance:
[View](#)

REACH 241:
[Contains SVHC\(s\)](#)