

TECHSPEC®

30mm, Side Drive, Standard Top, 0.5" Travel, English Micrometer



Stock #66-389

3-4 DAYS

-

1

+

£307.70

ADD TO CART

Qty 1-2

£307.70

Qty 3+

£268.34

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Linear (X)

Guide System:
Crossed Roller Bearing

Type of Drive:
English Micrometer

Drive Orientation:

Side Drive
Type: English
Stage Size (mm): 30 x 30
Travel (inches): 0.5
Center Hole: ¼-20
Construction: Aluminium Stage
Leadscrew Pitch (mm): 0.635
Load Capacity (kg): 3
Mounting Threads: (1) ¼-20, (6) 2-56
Stage Size (inches): 1.18 x 1.18
Straight Line Accuracy (µm): 2
Pitch (arcsec): 30
Yaw (arcsec): 25

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 233: Contains SVHC(s)