

40mm Precision Stage, English Dovetail Carrier



40mm Precision Stage, English Dovetail Carrier

Stock #12-510 3-4 DAYS

-

1

+

£100.30

ADD TO CART

Qty 1-9

£100.30

Qty 10+

£88.74

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Linear (X)

Guide System:
Dovetail

Type of Drive:
Manual

Type: English
Length (inches): 1.57
Length (mm): 40.00
Construction: Black Anodized Aluminum
Mounting Threads: (4) 6-32, (8) 2-56, (1) 1/4-20
Note: Carrier

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant