

50.8mm Dia. Right-Handed Plastic Circular Polarizer (CP42HER)



Stock **#88-102**

3-4 DAYS

-

1

+

£57.80

ADD TO CART

Qty 1-5
£57.80
Qty 6+
£48.45
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
50.80

Substrate:

[CP42HER on PMMA](#)

Operating Temperature (°C):
-40 to +80

Thickness (mm):

2.29 ±0.24
Transmission (%) : 42.00
Type : Right-Handed Circular Polarizer
Dimensional Tolerance (mm) : +0.0/-0.5
Construction : Polarizing Film on PMMA
Wavelength Range (nm) : 400 - 700
Polarization Efficiency (%) : >99.90
Heat Resistance (°C x Hours) : 80 x 500
#Sorting : 8.00

Regulatory Compliance

RoHS 2015 : Compliant
Certificate of Conformance : View
Reach 235 : Compliant