

TECHSPEC® 50mm NIR, Polarizing Cube Beamsplitter



TECHSPEC® Broadband Polarizing Cube Beamsplitters

Stock #65-606 3-4 DAYS

-

1

+

£828.75

ADD TO CART

Qty 1-5

£828.75

Qty 6+

£663.00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Beam Deviation (arcmin):
±3

Clear Aperture (%):
90

Coating Specification:
R_{avg} <0.5% @ 700 - 1100nm

Construction: Cube
Dimensions (mm): 50.0 x 50.0 x 50.0 ±0.1
Extinction Ratio: 500:1
P-Polarization Transmission (%): >90
S-Polarization Reflection (%): >99
Substrate: N-SF11
Surface Quality: 40-20
Type: Linear Polarizer
Wavelength Range (nm): 700 - 1100
Power (fringes) @ 632.8nm: 1.25
Irregularity (fringes) @ 632.8nm: 0.25

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View