

5.8mm CA, A-58N0-P19 Corning® Varioptic® Variable Focus Liquid Lens, Packaged A-Series - 6 pins FPC without Thermistor



5.8mm CA, A-58N0-P19 Corning® Varioptic® Variable Focus Liquid Lens, Packaged A-Series - 6 pins FPC without Thermistor



Stock **#16-035** CLEARANCE 3-4 DAYS

-

1

+

£197.16

ADD TO CART

Qty 1+

£197.16

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
15.50

Coating:
VS

Type: Packaged Lens
Clear Aperture CA (mm): 5.8
Contents of Kit: Packaged A-58N0 with a bent flex cable without populated thermistor FPC-A-19 (6 pins)
Focus Range: -5 to +10 diopter
Model Number: A-58N0-P19
Operating Temperature (°C): -20 to +50
Storage Temperature (°C): -40 to +85
Thickness (mm): 6.30
Transmission (%): 97 @ 587nm
Transmitted Wavefront Error, RMS: 80nm
Typical Applications: Optical instruments such as ophthalmology, scientific instrumentation, life sciences and microscopes requiring a larger clear aperture than the A-39N lens

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View