

600 Grooves, 25mm Sq, 28.7° Groove Angle Grating



Stock #49-580

3-4 DAYS

-

1

+

£102.00

ADD TO CART

Qty 1-9
£102.00
Qty 10+
£91.80
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Groove Density (grooves/mm):
600

Wavelength Range (nm):
400 - 700

Blaze Angle (°):
28.7

Dimensions (mm): 25.00 x25.00
Construction: Blazed (Ruled) Grating
Length (mm): 25.00
Substrate: ☐ B270
Thickness (mm): 3.00 ±0.5
Type: Transmission Diffraction Grating
Wavelength: VIS
Width (mm): 25.00
Alignment of Grooves to Edge (°): ±0.5
Groove Angle (°): 28.7

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View