

600 Grooves, 25mm Square, 750nm Ruled Diffraction Grating



Reflective Ruled Diffraction Gratings

Stock #41-028 ☐ In Stock

-

1

+

£113.90

ADD TO CART

Qty 1+

£113.90

Volume Pricing

[Request Quote](#)

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Groove Density (grooves/mm):
600

Blaze Wavelength (nm):
750

Blaze Angle (°):
13.00

Dimensions (mm):
25.0 x 25.0 ±0.5

Clear Aperture (%) : 90
Coating : Bare Aluminum
Construction : Ruled Grating
Direction of Grooves : Parallel to Short Dimension
Length (mm) : 25.00
Substrate : ☐ Float Glass
Thickness (mm) : 9.50 ±0.5
Type : Reflective Diffraction Grating
Width (mm) : 25.00
Alignment of Grooves to Edge (°) : ±0.5
Absolute Peak Efficiency, Typical (%) : 75
Peak Efficiency Avg, Typical (%) : >70

Regulatory Compliance

RoHS 2015 : Compliant
Reach 219 : Compliant
Certificate of Conformance : View
