

636nm CWL, 10nm FWHM, 50mm Mounted Diameter



Stock #86-633

3-4 DAYS

-

1

+

£377.40

ADD TO CART

Qty 1-9

£377.40

Qty 10+

£339.15

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):

50.00 +0.0/-0.2

Angle of Incidence (°):

0

Optical Density OD (Average):

≥3.0

Clear Aperture CA (mm): 42.0
Center Wavelength CWL (nm): 636.00 ±2
Center Wavelength CWL Tolerance (nm): ±2
Full Width-Half Max FWHM (nm): 10.00 ±2
Full Width-Half Max FWHM Tolerance (nm): ±2
Minimum Transmission (%): ≥45
Operating Temperature (°C): -50 to +75
Coating: Traditional Coated
Surface Quality: 80-50
Thickness Tolerance (mm): ±0.1
Type: Bandpass Filter
Typical Applications: Zn Emission Line
Blocking Wavelength Range (nm): 200 - 1200
Construction: Mounted in Black Anodized Ring
Mount Thickness (mm): 7.5 ±0.1

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View