

TECHSPEC[®] 65mm X-Y Positioning Stage



65mm X-Y Positioning Stage

Stock #12-832 3-4 DAYS



1



£405.45

ADD TO CART

Qty 1-4

£405.45

Qty 5+

£378.08

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Linear (X-Y)

Guide System:
Ball Slide

Type of Drive:
Rack and Pinion

Drive Orientation: Center Drive
Type: Universal
Travel (mm): 25 (±12.5mm) in X and Y
Travel (inches): 0.98 (±0.49) in X and Y
Load Capacity, Normal (kg): 5
Mounting Threads: (4) M4 x 0.7
Note: Movement
Straight Line Accuracy (µm): 50
Travel Per Knob Rotation (mm): 18

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View