

6" White Advanced Illumination High Intensity Ring Light

See More by [Advanced Illumination](#)



Stock **#88-490** [CONTACT US](#)



1



£1,124.55

ADD TO CART

Qty 1+

£1,124.55

Volume Pricing

[Request Quote](#)

 Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Color:
White

Diameter (mm):
152.40

Height (mm):

26.7
Inner Diameter (mm): 66.00
Model Number: RL113-WHI-IC
Operating Temperature (°C): 0 to 60
Outer Diameter (mm): 152.4
Weight (g): 681.00
Working Distance (mm): 225 - 600
LED Lifetime (hours): 50,000
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-773 China: #66-855
Number of Channels: 1.00
Type of Illumination: LED Illuminator
Note: Optional Manual Intensity Adjustment #86-887 and #89-555 are Available
Manufacturer: Advanced Illumination
Geometry: Ring Light
Illumination Mode: Constant
Environmental Rating: IP67

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Contains SVHC(s)
