

76.2mm Dia., Aluminum Coated, Aluminum Substrate Mirror



Stock #47-119 3-4 DAYS

-

1

+

£459.85

ADD TO CART

Qty 1-5

£459.85

Qty 6+

£413.86

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
76.20 +0.00/-0.38

Substrate: ☐
Aluminum 6061-T6

Surface Quality:

80-50
Coating Specification: R_{avg} >85% @ 400 - 700nm R_{avg} >70% @ 700 - 2000nm R_{avg} >97% @ 2 - 12μm
Coating: Protected Aluminum (400-12000nm)
Coating Type: Metal
Clear Aperture (%): 90
Mounting Threads: 8-32 TPI Tapped Holes
Surface Roughness (Angstroms): <175
Thickness (mm): 12.70
Type: Flat Mirror
Wavelength Range (μm): 0.4 - 12
Wavelength Range (nm): 400 - 12000
Surface Flatness (RMS): λ/2

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant