

60mm Max. Aperture, Burnished Steel Leaves Iris Diaphragm



Standard Series

Stock #57-585

3-4 DAYS



1



£172.55

ADD TO CART

Qty 1-4

£172.55

Qty 5+

£152.15

Volume Pricing

[Request Quote](#)

!

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type:
Unmounted

Minimum Aperture (mm):
4.0, Typical

Maximum Aperture (mm):
60.0

Outer Diameter (mm): 82.0
Construction: Anodized Aluminum Alloy, Burnished Spring Steel Leaves
Lever Diameter (mm): 3.00
Lever Length (mm): 13.00
Number of Leaves: 17.00
Thickness (mm): 8.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant
