


[All Products](#) / [Optics](#) / [Optical Filters](#) / [Shortpass Filters](#) / [OD 2.0 Shortpass Filters](#)

[See all 36 Products in Family](#)

950nm, 25mm Dia., OD 2.0 Shortpass Filter

950nm, 25mm Dia., OD 2.0 Shortpass Filter



OD 2.0 Shortpass Filters

Stock #15-266 3-4 DAYS

 1 

£88.40

ADD TO CART

Qty 1-9

£88.40

Qty 10+

£79.56

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 +0.00/-0.20

Angle of Incidence (°):
0

Optical Density OD (Average):
≥2.0

Cut-Off Wavelength (nm): 950.00 ±19
Substrate: 
Coating: Hard Coated
Rejection Wavelength (nm): 1025 - 1250
Surface Quality: 60-40
Thickness (mm): 2.00 ±0.10
Transmission (%): ≥85
Transmission Wavelength (nm): 500 - 900
Type: Shortpass Filter
Clear Aperture (%): 90
Environmental Durability: ML-STD-810F, Section 507.4
Physical Durability: ML-C-48497A, Section 3.4.1
Wavelength Range (nm): 500 - 1250

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View