

[All Products](#) / [Cameras](#) / [USB Cameras](#) / [Basler ace USB 3.0 Cameras](#)

[See all 58 Products in Family](#)

Basler ace acA1440-220um USB 3.0 Monochrome Camera



Stock **#11-500** 3-4 DAYS

[Similar Cameras](#)



1



£347.65

ADD TO CART

Qty 1+

£347.65

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Video Output:
USB 3.0

Type:
Monochrome Camera

Manufacturer:
Basler

Mounting Threads: ¼-20 with Tripod Mount Adapter #88-517
Image Buffer: Not Specified
Camera Family: ace
Model Number: acA1440-220um
Imaging Sensor: Sony IMX273
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Global
Camera Sensor Format: 1/2.9"
Resolution (MegaPixels): 1.60
Pixels (H x V): 1,440 x 1,080
Pixel Size, H x V (µm): 3.45 x 3.45
Sensing Area, H x V (mm): 4.97 x 3.73
Frame Rate (fps): 227.00
Pixel Depth: 10/12 bit
Exposure Time: Freely Programmable
Connector: USB 3.0, Micro-B with Screw Locks
Power Supply: Power over USB
Power Consumption (W): 3.3
GPIOs: 1 opto-coupled input line, 1 opto-coupled output line, 2 general purpose I/O (GPIO) lines
Synchronization: Hardware Trigger (GPIO), Software Trigger, or Free-Run
Dimensions (mm): 29.3 x 29 x 29 (excludes connectors and lens mount)
Weight (g): 80
Mount: C-Mount
Housing: Full
Interface Port Orientation: Back Panel
Dynamic Range (dB): 71.5
Operating Temperature (°C): 0 to +50
Storage Temperature (°C): -20 to +80
GPIO Connector Type: 6-pin Hirose (HR10)
Machine Vision Standard: USB3 Vision v1.0
Operating System: Software Driver: Windows, Linux - 32 and 64 bit

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant

