

Basler ace acA1920-25um Monochrome USB 3.0 Camera



Stock **#89-983**

3-4 DAYS

Similar Cameras



1



£296.65

ADD TO CART

Qty 1+

£296.65

Volume Pricing

Request Quote

Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use |

Learn More

Get Product Downloads

Video Output:

USB 3.0

Type:

Monochrome Camera

Manufacturer:

Basler
Mounting Threads: 1/4-20 with Tripod Mount Adapter #88-517
Image Buffer: Not Specified
Camera Family: ace
Model Number: acA1920-25um
Imaging Sensor: ON Semi MT9P031
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Rolling
Camera Sensor Format: 1/3.7"
Resolution (MegaPixels): 2.00
Pixels (H x V): 1,920 x 1,080
Pixel Size, H x V (µm): 2.2 x 2.2
Sensing Area, H x V (mm): 4.22 x 2.38
Frame Rate (fps): 25.00
Pixel Depth: 12 bit
Exposure Time: Freely Programmable
Connector: USB 3.0, Micro-B with Screw Locks
Power Supply: Power over USB
Power Consumption (W): 2.2
GPIOs: 1 opto-coupled input line, 1 opto-coupled output line, 2 general purpose I/O (GPIO) lines
Synchronization: Hardware Trigger (GPIO) or Free-Run
Dimensions (mm): 29.3 x 29 x 29 (excludes connectors and lens mount)
Weight (g): 80
Mount: C-Mount
Housing: Full
Interface Port Orientation: Back Panel
Dynamic Range (dB): 60.3
Operating Temperature (°C): 0 to +50
Storage Temperature (°C): -20 to +80
GPIO Connector Type: 6-pin Hirose (HR10)
Machine Vision Standard: USB3 Vision v1.0
Operating System: Software Driver: Windows 32 and 64 bit, Linux, OS X

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant

